

### 304 Stainless Steel Enviroline® Series Enclosures

#### Application -

Designed to house electrical and electronic controls, instruments and components in areas which may be regularly hosed down or are in very wet conditions. Provides protection from dust, dirt, oil, and water. For outdoor application, a drip shield is recommended. For installation information, consult our Installation Manual at [www.saginawcontrol.com](http://www.saginawcontrol.com).

#### Construction -

- 0.075" stainless steel Type 304.
- Seams continuously welded and ground smooth.
- Flange through collar around all sides of door opening.
- Oil-resistant gasket.
- Collar studs provided for mounting optional sub-panels.
- Stainless steel interchangeable doors.
- Removable and interchangeable doors.
- Black quarter turn latches.
- Latches are opened or closed with a screwdriver (optional tamper-resistant inserts are available).
- Mounting holes in back of enclosure.
- Mounting hardware, sealing washer and hole plug included.
- Removable print pocket.
- Ground studs on door and body.

#### Options -


- Optional mounting feet available.
- Door hardware available.

#### Finish -

#4 brushed finish on all exterior surfaces. Optional sub-panels are powder coated white.

#### ISE - Industry Standards -

NEHA Type 4, 4X, 72 & Type 13  
UL Listed Type 4, 4X & 12  
CSA Type 4, 4X & 12  
IEC 60529 IP66





### 304 STAINLESS STEEL ENVIROLINE® SERIES ENCLOSURES

Catalog No.	ENCLOSURE PRODUCT CODE SS			List Price	SUB-PANEL (P3)		List Price	
	Height (A)	Width (B)	Depth (C)		Catalog No.	Panel Height (D)		Panel Width (E)
SCE-12EL1206SSLP	12.00	12.00	6.00	ISS 536.16	SCE-12DLP12	9.00	21.00	13.67
SCE-12EL2406SSLP	12.00	24.00	6.00	ISS 712.62	SCE-12P24	9.00	21.00	27.66
SCE-16EL1206SSLP	16.00	12.00	6.00	ISS 580.45	SCE-16P12	13.00	9.00	14.81
SCE-16EL1206SSLP	16.00	12.00	8.00	ISS 631.18	SCE-16P12	13.00	9.00	14.81
SCE-16EL1606SSLP	16.00	16.00	6.00	ISS 654.26	SCE-16P16	13.00	13.00	24.57
SCE-16EL1606SSLP	16.00	16.00	8.00	ISS 688.19	SCE-16P16	13.00	13.00	24.57
SCE-20EL1606SSLP	20.00	16.00	6.00	ISS 770.98	SCE-20P16	17.00	13.00	30.37
SCE-20EL1606SSLP	20.00	16.00	8.00	ISS 770.98	SCE-20P16	17.00	13.00	30.37
SCE-20EL1610SSLP	20.00	16.00	10.00	ISS 822.57	SCE-20P16	17.00	13.00	30.37
SCE-20EL2006SSLP	20.00	20.00	6.00	ISS 794.06	SCE-20P20	17.00	17.00	35.44
SCE-20EL2006SSLP	20.00	20.00	8.00	ISS 853.79	SCE-20P20	17.00	17.00	35.44
SCE-20EL2010SSLP	20.00	20.00	10.00	ISS 909.44	SCE-20P20	17.00	17.00	35.44
SCE-24EL1606SSLP	24.00	16.00	6.00	ISS 933.87	SCE-24P20	21.00	17.00	45.57
SCE-24EL1606SSLP	24.00	16.00	8.00	ISS 840.20	SCE-24P16	21.00	13.00	32.92
SCE-24EL2006SSLP	24.00	20.00	6.00	ISS 880.43	SCE-24P20	21.00	17.00	45.57
SCE-24EL2006SSLP	24.00	20.00	8.00	ISS 933.87	SCE-24P20	21.00	17.00	45.57
SCE-24EL2406SSLP	24.00	24.00	6.00	ISS 1,026.17	SCE-24P24	21.00	21.00	53.18
SCE-24EL2406SSLP	24.00	24.00	8.00	ISS 1,086.74	SCE-24P24	21.00	21.00	53.18
SCE-24EL2410SSLP	24.00	24.00	10.00	ISS 1,167.34	SCE-24P24	21.00	21.00	53.18
SCE-24EL2410SSLP	24.00	24.00	12.00	ISS 1,323.43	SCE-24P24	21.00	21.00	53.18
SCE-24EL3006SSLP	24.00	30.00	6.00	ISS 1,165.97	SCE-30P24	27.00	21.00	63.29
SCE-24EL3010SSLP	24.00	30.00	10.00	ISS 1,254.20	SCE-30P24	27.00	21.00	63.29
SCE-30EL1606SSLP	30.00	16.00	6.00	ISS 977.30	SCE-30P16	27.00	13.00	46.57
SCE-30EL2006SSLP	30.00	20.00	6.00	ISS 1,056.74	SCE-30P20	27.00	17.00	55.70
SCE-30EL2010SSLP	30.00	20.00	10.00	ISS 1,146.97	SCE-30P20	27.00	17.00	55.70
SCE-30EL2406SSLP	30.00	24.00	6.00	ISS 1,167.34	SCE-30P24	27.00	21.00	63.29
SCE-30EL2410SSLP	30.00	24.00	10.00	ISS 1,255.56	SCE-30P24	27.00	21.00	63.29
SCE-30EL2412SSLP	30.00	24.00	12.00	ISS 1,330.21	SCE-30P24	27.00	21.00	63.29
SCE-30EL3006SSLP	30.00	30.00	6.00	ISS 1,455.95	SCE-30P30	27.00	27.00	83.55
SCE-30EL3006SSLP	30.00	30.00	8.00	ISS 1,337.00	SCE-30P30	27.00	27.00	83.55
SCE-30EL3010SSLP	30.00	30.00	10.00	ISS 1,418.45	SCE-30P30	27.00	27.00	83.55
SCE-30EL3012SSLP	30.00	30.00	12.00	ISS 1,506.57	SCE-30P30	27.00	27.00	83.55
SCE-36EL13006SSLP	36.00	36.00	6.00	ISS 1,495.82	SCE-36P30	33.00	27.00	101.27
SCE-36EL2406SSLP	36.00	24.00	6.00	ISS 1,316.54	SCE-36P24	33.00	21.00	75.96
SCE-36EL2410SSLP	36.00	24.00	10.00	ISS 1,494.88	SCE-36P24	33.00	21.00	75.96
SCE-36EL3006SSLP	36.00	30.00	6.00	ISS 1,495.82	SCE-36P30	33.00	27.00	101.27
SCE-36EL3010SSLP	36.00	30.00	10.00	ISS 1,607.12	SCE-36P30	33.00	27.00	101.27
SCE-36EL3012SSLP	36.00	30.00	12.00	ISS 1,703.48	SCE-36P30	33.00	27.00	101.27
SCE-36EL3606SSLP	36.00	36.00	6.00	ISS 1,737.36	SCE-36P36	33.00	33.00	118.99
SCE-36EL3606SSLP	36.00	36.00	8.00	ISS 1,737.36	SCE-36P36	33.00	33.00	118.99
SCE-36EL3612SSLP	36.00	36.00	12.00	ISS 1,913.89	SCE-36P36	33.00	33.00	118.99
SCE-42EL12410SSLP	42.00	24.00	10.00	ISS 1,628.84	SCE-42P24	39.00	21.00	91.14
SCE-42EL3010SSLP	42.00	30.00	10.00	ISS 1,763.57	SCE-42P30	39.00	27.00	116.47
SCE-42EL3612SSLP	42.00	36.00	12.00	ISS 2,106.63	SCE-42P36	39.00	33.00	136.72
SCE-48EL13612SSLP	48.00	36.00	12.00	ISS 2,236.93	SCE-42P36	39.00	33.00	136.72
SCE-48EL3612SSLP	48.00	36.00	12.00	ISS 2,334.67	SCE-48P36	45.00	33.00	154.46
SCE-60EL3612SSLP	60.00	36.00	12.00	ISS 2,545.05	SCE-48P36	45.00	33.00	154.46
SCE-60EL3612SSLP	60.00	36.00	12.00	ISS 2,755.44	SCE-60P36	57.00	33.00	189.89
SCE-60EL3616SSLP	60.00	36.00	16.00	ISS 2,972.63	SCE-60P36	57.00	33.00	189.89
SCE-60EL3624SSLP	60.00	36.00	24.00	ISS 3,580.50	SCE-60P36	57.00	33.00	189.89
SCE-72EL3016SSLP	72.00	30.00	16.00	ISS 3,189.61	SCE-72P30	66.00	27.00	210.15
SCE-72EL3612SSLP	72.00	36.00	12.00	ISS 3,278.03	SCE-72P36	66.00	33.00	225.33
SCE-72EL3616SSLP	72.00	36.00	16.00	ISS 3,461.27	SCE-72P36	66.00	33.00	225.33

### STAINLESS STEEL ENVIROLINE® SERIES ENCLOSURES

#### TECHNICAL DATA



**SUB-PANEL NOTES:**  
 Catches must be from the inside of the door  
 C = 0.18 (4.5) for bent sub-panels

**LATCH NOTES:**  
 Enclosures < 609.6 in height require only one latch centered on door.  
 Enclosures >= 24.00" (609.6) and < 40.00" (1016) in height require two latches on door.  
 Enclosures >= 40.00" (1016) require three latches on door.  
 Omit center latch top and bottom of door when door width is <= 30.00" (762)

#### SECTION A-A

Back to SS Hail-Mount Enclosures

Phone (989) 799-6871  
 Fax (989) 799-4524

